

LUMINA

AA23POI050L51-10 9011/9011

EAN 4031582413038



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Lumina
Type	Swivel caster with intermittent brake
Load capacity at 1.8 mph	88.18 lb
Electric conductive	no
Stainless	no
Load capacity Static	176.37 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	2.17 in
Overall width	2.17 in
Overall weight	0.14 lb

HOUSING

Housing Material	Polypropylene
Fork shape	Twin wheel housing, closed
Swivel bearing	Stem, swiveling
Housing Color	Graphite black (RAL9011)
Offset	0.79 in
Swivel radius	2.05 in
Swivel interference	4.09 in
Dome diameter	0 in

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Tread color	Graphite black (RAL9011)
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.31 in
Axle hole diameter	0 in
Hub length	0 in
Body width	0.31 in
Hardness of tread (D)	65 Shore D

FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	0.39 in

LUMINA

AA23POI050L51-10 9011/9011

EAN 4031582413038



BETTER MOBILITY. BETTER LIFE.

Product Drawings

