

# BASETECH

POO160X40-Ø20 RAL9011

EAN 4031582488647



Image may differ from the original product

## WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	160 mm
Tread width	40 mm
Axle hole diameter	20 mm
Hub length	58 mm
Hardness of tread (D)	65 Shore D

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Basetech
Housing type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	200 kg
Load capacity Static	400 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.177 kg

# BASETECH

POO160X40-Ø20 RAL9011

EAN 4031582488647



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

