

ALPHA

3478PIJ100P62

EAN 4031582335521
Order number 00001242



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ● ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Alpha |
| Type | Fixed castor |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph | 165.35 lb |
| Load capacity Static | 330.69 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 5.04 in |
| Overall width | 3.35 in |
| Overall weight | 1.18 lb |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polypropylene |
| Tread material | Solid rubber, non-marking |
| Bearing | Roller bearing |
| Axle | Screwed with nut |
| Wheel color | Graphite black (RAL9011) |
| Threadguards | With threadguard |
| Diameter | 3.94 in |
| Tread width | 1.38 in |
| Body width | 1.38 in |
| Hardness of tread (A) | 80 Shore A |

HOUSING

| | |
|------------|--------------------|
| Material | Steel sheet, heavy |
| Fork shape | Broad |
| Color | Blue passivated |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 4.06 in |
| Plate width | 3.35 in |
| Plate hole length (Minimum) | 3.03 in |
| Plate hole length (Maximum) | 2.36 in |
| Plate hole width (Minimum) | 3.03 in |
| Plate hole width (Maximum) | 3.15 in |
| Plate hole diameter | 0.35 in |

ALPHA

3478PIJ100P62

EAN 4031582335521
Order number 00001242



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

