

PRODUCT INFORMATION

# NOVATECH

ITP 100X50-Ø20 HL60 CV

EAN 4031582377132  
Order number 00838828



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Aluminum               |
|                       | convex                 |
| Tread material        | Polyurethane, casted   |
| Bearing               | Precision ball bearing |
| Wheel color           | Honey yellow (RAL1005) |
| Threadguards          | Without threadguard    |
| Diameter              | 3.94 in                |
| Tread width           | 1.97 in                |
| Axle hole diameter    | 0.79 in                |
| Hub length            | 2.36 in                |
| Body width            | 1.97 in                |
| Hardness of tread (A) | 92 Shore A             |
| Hardness of tread (D) | 42 Shore D             |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Novatech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 992.08 lb                     |
| Load capacity at 3.7 mph    | 793.66 lb                     |
| Load capacity Static        | 1984.16 lb                    |
| Temperature range (Minimum) | 14 °F                         |
| Temperature range (Maximum) | 140 °F                        |
| Overall weight              | 1.37 lb                       |

# NOVATECH

ITP 100X50-Ø20 HL60 CV

EAN 4031582377132  
Order number 00838828



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

