

MAXTECH

PNP 200X30-Ø8 HL60

EAN 4031582320633
Order number 00005569



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Polyurethane, foamed
Bearing	Precision ball bearing
Wheel color	Black
Threadguards	With threadguard
Diameter	200 mm
Tread width	30 mm
Axle hole diameter	8 mm
Hub length	60 mm
Body width	30 mm
Hardness of tread (A)	70 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.4 kg

PRODUCT INFORMATION

MAXTECH

PNP 200X30-Ø8 HL60

EAN 4031582320633
Order number 00005569



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

