

PURETECH AIR

DQR400x100-Ø25 HL74 4PR

EAN 4031582318203



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Tread hardness	soft
Body material	Sheet Steel
Tread material	Pneumatic tire, block profile
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	15.75 in
Tread width	3.94 in
Axle hole diameter	0.98 in
Hub length	2.91 in
Hardness of tread (A)	55 Shore A

PERFORMANCE

Roll Performance	● ○ ○ ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech air
Type	Wheel
Load capacity at 1.8 mph	440.92 lb
Electric conductive	no
Stainless	no
Load capacity Static	881.85 lb
Overall weight	5.38 lb

PURETECH AIR

DQR400x100-Ø25 HL74 4PR

EAN 4031582318203



BETTER MOBILITY. BETTER LIFE.

Product Drawings

