

# PURETECH

PVR 200X50-Ø25

EAN 4031582321319  
Order number 00050597



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
Tread material	Solid rubber, black
Bearing	Roller bearing
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	200 mm
Tread width	50 mm
Axle hole diameter	25 mm
Hub length	58 mm
Body width	50 mm
Hardness of tread (A)	80 Shore A

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Puretech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	205 kg
Load capacity Static	410 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	1.17 kg

# PURETECH

PVR 200X50-Ø25

EAN 4031582321319  
Order number 00050597



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

