

NOVATECH

ITP 100X50-Ø25

EAN 4031582319866
Broj porudžbine 00830808

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Aluminijum
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
štitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	50 mm
dimenzija rupa osovina	25 mm
dužina glavcine	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	540 kg
Nosivost na 6 km/h	430 kg
Statički Nosivost	1080 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,592 kg

NOVATECH

ITP 100X50-Ø25

EAN 4031582319866
Broj porudžbine 00830808



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

