

PRODUCT INFORMATION

# ELASTECH

UFR125x40-Ø15

EAN 4031582337969



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### WHEEL

Body material	Polyamide
Tread Material Mix	Elastic tire, non-marking, vulcanized
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	125 mm
Tread width	40 mm
Axle Hole Diameter	15 mm
Hub Length	58 mm

### PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement Noise	● ● ● ● ● ●
Attrition	● ● ● ● ○ ○
Corrosion Resistance	● ● ● ● ○ ○

### CORE ATTRIBUTES

Product Name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	250 kg
Electric Conductive	No
Stainless	No
Load capacity Static	500 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	0.43 kg

# ELASTECH

UFR125x40-Ø15

EAN 4031582337969



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

