

NOVATECH

FTP 250X60-Ø25 HL62

EAN 4031582331066

Broj porudžbine 00803985



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Casting
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	250 mm
Širina omotac	60 mm
dimenzija rupa osovina	25 mm
dužina glavcine	62 mm
Širina tela	60 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	1680 kg
Nosivost na 6 km/h	1400 kg
Statički Nosivost	2800 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	7,123 kg

NOVATECH

FTP 250X60-Ø25 HL62

EAN 4031582331066
Broj porudžbine 00803985



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

