

# NOVATECH

ETY 060x20-Ø20 HL12

EAN 4031582318463



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product Name                | Novatech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 100 kg                        |
| Load capacity at 6 km/h     | 80 kg                         |
| Electric Conductive         | No                            |
| Stainless                   | No                            |
| Load capacity Static        | 200 kg                        |
| Temperature range (Minimum) | -10 °C                        |
| Temperature range (Maximum) | 60 °C                         |
| Overall weight              | 0.14 kg                       |

## WHEEL

|                       |                                 |
|-----------------------|---------------------------------|
| Body material         | Steel, iron                     |
| Tread Material Mix    | Polyurethane, casted            |
| Bearing               | Precision ball bearing (RS/2RS) |
| Wheel Color           | Honey yellow (RAL1005)          |
| Diameter              | 60 mm                           |
| Tread width           | 20 mm                           |
| Axle Hole Diameter    | 20 mm                           |
| Hub Length            | 12 mm                           |
| Body width            | 20 mm                           |
| Hardness of tread (A) | 92 Shore A                      |
| Hardness of tread (D) | 42 Shore D                      |

