

# FOOTMASTER

## FOOT MASTER GAGD-150-ASF-HUD

EAN 4031582496574  
Order number 00800208



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ○ ○ ○ ○ ○ |
| Movement noise       | ○ ○ ○ ○ ○ |
| Attrition            | ○ ○ ○ ○ ○ |
| Corrosion resistance | ○ ○ ○ ○ ○ |

### CORE ATTRIBUTES

|                             |               |
|-----------------------------|---------------|
| Product name                | Footmaster    |
| Type                        | Swivel castor |
| Load capacity at 3 km/h     | 630 kg        |
| Temperature range (Minimum) | -10 °C        |
| Temperature range (Maximum) | 90 °C         |
| Overall height              | 200 mm        |
| Overall width               | 141 mm        |
| Overall weight              | 13.953 kg     |

### WHEEL

|             |                |
|-------------|----------------|
| Bearing     | Unmachined hub |
| Diameter    | 150 mm         |
| Tread width | 40 mm          |
| Body width  | 40 mm          |

### HOUSING

|                     |        |
|---------------------|--------|
| Offset              | 35 mm  |
| Swivel radius       | 115 mm |
| Swivel interference | 230 mm |
| Dome diameter       | 130 mm |

### FITTING

|                             |        |
|-----------------------------|--------|
| Plate length                | 145 mm |
| Plate width                 | 145 mm |
| Plate hole length (Maximum) | 120 mm |
| Plate hole width (Maximum)  | 120 mm |
| Plate hole diameter         | 11 mm  |

# FOOTMASTER

FOOT MASTER GAGD-150-ASF-HUD

EAN 4031582496574  
Order number 00800208



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

