

LINEA LIGHT

5925PJI075L51-10 RAL7001 KICK PEDAL

EAN 4031582377507



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ● |
| Movement noise | ● ● ● ● ● |
| Attrition | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ● |

CORE ATTRIBUTES

| | |
|-----------------------------|--------------------------------|
| Product name | Linea light |
| Housing type | Swivel castor with wheel brake |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 3 km/h | 60 kg |
| Load capacity Static | 120 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 75.5 mm |
| Overall width | 55 mm |
| Overall weight | 0.155 kg |

WHEEL

| | |
|-----------------------|--------------------------------|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Plain bearing with spacer tube |
| Threadguards | Without threadguard |
| Diameter | 75 mm |
| Tread width | 15 mm |
| Hardness of tread (A) | 92 Shore A |

HOUSING

| | |
|---------------------|--------------------|
| Material fork | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel bearing | Stem, swiveling |
| Offset | 23 mm |
| Swivel radius | 82 mm |
| Swivel interference | 164 mm |
| Dome diameter | 30 mm |

FITTING

| | |
|--------------------|----------------------------|
| Fitting type | Blind hole for B10 fitting |
| Bolt hole diameter | 10 mm |



LINEA LIGHT


5925PJI075L51-10 RAL7001 KICK PEDAL

EAN 4031582377507



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS



Deutscher
Designer
Club



Interzum
Award



IF
Design
Award