

MAXTECH

PAO100X25-Ø6X27 + ASBUS

EAN 4031582381245



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Load capacity at 1.8 mph	154.32 lb
Load capacity Static	308.65 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.24 lb

WHEEL

Diameter	3.94 in
Tread width	0.98 in
Axle hole diameter	0.24 in
Hub length	1.06 in