

# MAXTECH

PAO100X25-Ø6X27 + ASBUS

EAN 4031582381245



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Load capacity at 1.8 mph	154.32 lb
Load capacity Static	308.65 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.24 lb

## WHEEL

Diameter	3.94 in
Tread width	0.98 in
Axle hole diameter	0.24 in
Hub length	1.06 in