PRODUCT INFORMATION

# LEVINA

5371PJP100P51 7001/6032

EAN 4031582358704

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement noise | ●●●●○ |
| Attrition | ●●●○○ |
| Corrosion resistance | ●●●●○ |

## CORE ATTRIBUTES

| | |
|---|---|
| Product name | Levina |
| Type | Swivel caster with directional lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 220.46 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 440.92 lb |
| Temperature range (Minimum) | 14 °F |
| Temperature range (Maximum) | 104 °F |
| Overall height | 5.55 in |
| Overall width | 2.32 in |
| Overall weight | 1.16 lb |

## HOUSING

| | |
|---|---|
| Housing Material | Polyamide |
| Fork shape | Slim |
| Swivel bearing | Two ball races |
| Housing Color | Silver gray (RAL7001) |
| Offset | 1.42 in |
| Swivel radius | 3.86 in |
| Swivel interference | 7.72 in |
| Dome diameter | 2.32 in |

## WHEEL

| | |
|---|---|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Precision ball bearing |
| Wheel color | Silver gray (RAL7001) |
| Threadguards | With threadguard |
| Diameter | 3.94 in |
| Tread width | 1.26 in |
| Body width | 1.26 in |
| Hardness of tread (A) | 87 Shore A |

## FITTING

| | |
|---|---|
| Fitting type | Rectangular plate |
| Plate length | 3.74 in |
| Plate width | 2.76 in |
| Plate hole length (Maximum) | 1.97 in |
| Plate hole width (Maximum) | 2.95 in |
| Plate hole diameter | 0.43 in |

Universal Design Award

Deutscher Designer Club

© Copyright 2026 TENTE International GmbH


# LEVINA


5371PJP100P51 7001/6032


EAN 4031582358704


Order number 00061720

**Product Drawings**






Universal Design Award
Deutscher Designer Club

© Copyright 2026 TENTE International GmbH