

GALEA STAINLESS

5080YGC125R05-22X40

EAN 4031582355765
Order number 00772118



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	●●●○○
Movement noise	●●●○○
Attrition	●●●○○
Corrosion resistance	●●●●●

CORE ATTRIBUTES

Product name	Galea stainless
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	220.46 lb
Electric conductive	✓
Stainless	✓
Load capacity Static	440.92 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	6.38 in
Overall width	2.56 in
Overall weight	1.41 lb

WHEEL

Body material	Polypropylene, electric conductive
Tread material	Thermoplastic rubber, electric-conductive
Bearing	Precision ball bearing, stainless
Tread color	Traffic gray A (RAL7042)
Wheel color	Traffic gray A (RAL7042)
Threadguards	With threadguard
Diameter	4.92 in
Tread width	1.18 in
Body width	1.18 in
Hardness of tread (A)	90 Shore A

HOUSING

Material	Polyamide
Fork shape	Closed
Swivel bearing	Two ball races, reinforced or stainless
Color	Silver gray (RAL7001)
Offset	1.57 in
Swivel radius	3.74 in
Swivel interference	7.48 in
Dome diameter	2.32 in

FITTING

Fitting type	Solid stem, round
Bolt diameter	0.87 in
Bolt length	1.57 in

GALEA STAINLESS

5080YGC125R05-22X40

EAN 4031582355765
Order number 00772118



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

