

ZETA

4681ITP160P63 SOFT CV

EAN 4031582337631
Order number 00838060



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Zeta
Housing type	Swivel castor with directional lock
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1212.54 lb
Load capacity at 3.7 mph	970.03 lb
Load capacity Static	2425.08 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall height	7.87 in
Overall width	3.78 in
Overall weight	7.38 lb

WHEEL

Body material	Aluminum
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Traffic gray A (RAL7042)
Threadguards	Without threadguard
Diameter	6.3 in
Tread width	1.97 in
Body width	1.97 in
Hardness of tread (A)	80 Shore A

HOUSING

Material	Steel sheet, very heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Color	Blue passivated
Offset	2.17 in
Swivel radius	5.31 in
Swivel interference	10.63 in
Dome diameter	3.78 in

FITTING

Fitting type	Rectangular plate
Plate length	5.39 in
Plate width	4.13 in
Plate hole length (Minimum)	2.95 in
Plate hole length (Maximum)	3.15 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	4.13 in
Plate hole diameter	0.43 in

ZETA

4681ITP160P63 SOFT CV

EAN 4031582337631
Order number 00838060



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

