

ALPHA STAINLESS

8478UAD125P63 NATURAL/3004

EAN 4031582313222
Order number 00035529



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Alpha stainless
Housing type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	300 kg
Load capacity Static	600 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall height	161 mm
Overall width	115 mm
Overall weight	1.434 kg

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Roller bearing, stainless
Axle	Screwed with nut
Wheel color	Natural white
Diameter	125 mm
Tread width	40 mm
Body width	40 mm
Hardness of tread (A)	96 Shore A
Hardness of tread (D)	50 Shore D

HOUSING

Material fork	Stainless steel, heavy
Fork shape	Broad
Colour	Stainless steel
Stainless	✓

FITTING

Fitting type	Rectangular plate
Plate length	137 mm
Plate width	115 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

ALPHA STAINLESS


8478UAD125P63 NATURAL/3004

EAN 4031582313222
Order number 00035529



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS



8478UAD125 P63

