

COMPACTA

2198UOI045P60-67x24,5-TFR

EAN 4031582477542



BETTER MOBILITY. BETTER LIFE.

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Compacta
Type	Fixed caster
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	88.18 lb
Electric conductive	no
Stainless	no
Load capacity Static	176.37 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall height	1.91 in
Overall weight	0.14 lb

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Angular

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	1.77 in
Tread width	0.71 in
Hardness of tread (D)	75 Shore D

FITTING

Fitting type	Rectangular plate
Plate length	2.64 in
Plate width	0.96 in
Plate hole length (Maximum)	2.13 in
Plate hole width (Maximum)	2.13 in
Plate hole diameter	0.2 in

COMPACTA

2198UOI045P60-67x24,5-TFR

EAN 4031582477542



BETTER MOBILITY. BETTER LIFE.

Product Drawings

