

MONO

A020PJ1050L51-10 RAL7035

EAN 4031582359879



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Mono
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	66.14 lb
Load capacity Static	132.28 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	2.83 in
Overall weight	1.19 lb

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.71 in
Hardness of tread (A)	85 Shore A

HOUSING

Material	Polypropylene
Fork shape	Closed
Swivel bearing	Stem, swiveling
Color	Light gray (RAL7035)
Offset	0.98 in
Swivel radius	2.06 in
Swivel interference	4.11 in

FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	0.39 in

MONO

A020PJI050L51-10 RAL7035

EAN 4031582359879



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

