

PURETECH

PIP150x32-Ø8

EAN 4031582356694



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Puretech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	80 kg
Electric Conductive	No
Stainless	No
Load capacity Static	160 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.43 kg

WHEEL

Tread hardness	soft
Body material	Polypropylene
Tread Material Mix	Solid rubber, non-marking
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	150 mm
Tread width	32 mm
Axle Hole Diameter	8 mm
Hub Length	36.5 mm
Hardness of tread (A)	75 Shore A

PURETECH

PIP150x32-Ø8

EAN 4031582356694

Order number 00038560
Product Drawings



BETTER MOBILITY. BETTER LIFE.

