

NOVATECH

ETY 080X25-Ø25

EAN 4031582369427
Order number 00839178



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing (RS/2RS)
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	80 mm
Tread width	25 mm
Axle hole diameter	25 mm
Hub length	12 mm
Body width	25 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	160 kg
Load capacity at 6 km/h	130 kg
Load capacity Static	320 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	0.38 kg

TECHNICAL DRAWINGS

