

ZETA STAINLESS

8670UAD200P63

EAN 4031582313475
Order number 00830097



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Zeta stainless
Type	Swivel castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	500 kg
Load capacity at 6 km/h	400 kg
Stainless	✓
Load capacity Static	1000 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	80 °C
Overall height	240 mm
Overall width	96 mm
Overall weight	3.064 kg

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Roller bearing, stainless
Axle	Screwed with nut
Wheel color	Natural white
Diameter	200 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

HOUSING

Material fork	Stainless steel, heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races
Colour	Stainless steel
Offset	55 mm
Swivel radius	155 mm
Swivel interference	310 mm
Dome diameter	96 mm

FITTING

Fitting type	Medium rectangular plate
Plate length	137 mm
Plate width	105 mm
Plate hole length (Minimum)	74 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	74 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

ZETA STAINLESS

8670UAD200P63

EAN 4031582313475
Order number 00830097



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

