

# DURATECH SILENT

HUR100X36-Ø12 WHITE

EAN 4031582400687



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Damping, hybrid material
Tread material	Polyamide
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	100 mm
Tread width	36 mm
Axle hole diameter	12 mm
Hub length	44 mm
Hardness of tread (D)	75 Shore D

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Duratech silent
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	160 kg
Load capacity Static	320 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.4 kg

# DURATECH SILENT

HUR100X36-Ø12 WHITE

EAN 4031582400687



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

