

DURATECH

MOP 160X50-Ø30

EAN 4031582320046

Broj porudžbine 00801261



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid, super težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Bez stražara
Prečnik	160 mm
Širina omotac	50 mm
dimenzija rupa osovina	30 mm
dužina glavcine	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6306

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	2700 kg
Nosivost na 6 km/h	2250 kg
Statički Nosivost	4500 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	1,616 kg

DURATECH

MOP 160X50-Ø30

EAN 4031582320046
Broj porudžbine 00801261



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

