

# DURATECH

MOP 160X50-Ø30

EAN 4031582320046

Broj porudžbine 00801261



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	poliamid, super težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
štitnici omotaca	Bez stražara
Prečnik	160 mm
Širina omotac	50 mm
dimenzija rupa osovina	30 mm
dužina glavcine	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6306

## PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	2700 kg
Nosivost na 6 km/h	2250 kg
Statički Nosivost	4500 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	1,616 kg

# DURATECH

MOP 160X50-Ø30

EAN 4031582320046  
Broj porudžbine 00801261



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

