

# DURATECH HEAT

W00080X31 Ø12 TFR

EAN 4031582393842



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Thermoplastic synthetics, heat resistant
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	80 mm
Tread width	31 mm
Axle hole diameter	12 mm
Hub length	40 mm
Hardness of tread (D)	75 Shore D

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Duratech heat
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	200 kg
Load capacity Static	400 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	180 °C
Overall weight	0.078 kg

# DURATECH HEAT

W00080X31 Ø12 TFR

EAN 4031582393842



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

