

SOCKET

Kunststoff Huelse R20-19/11

EAN 4031582090123



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

FITTING

| | |
|---------------|-------------------------|
| Fitting type | Synthetic socket, round |
| Bolt diameter | 0.75 in |

PERFORMANCE

| | |
|----------------------|-----------|
| Corrosion resistance | ● ● ● ○ ○ |
|----------------------|-----------|

CORE ATTRIBUTES

| | |
|--------------------------|-----------|
| Product name | Socket |
| Type | Accessory |
| Load capacity at 1.8 mph | 88.18 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 176.37 lb |
| Overall height | 1.42 in |
| Overall weight | 0.01 lb |