

MAXTECH

PNP200x50-Ø8 HL60 GRIS

EAN 4031582452778



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement noise	● ● ● ● ○ ○
Attrition	● ● ● ● ○ ○
Corrosion resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	220.46 lb
Electric conductive	no
Stainless	no
Load capacity Static	440.92 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.14 lb

WHEEL

Tread hardness	soft
Body material	Polypropylene
Tread material	Polyurethane, foamed
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	7.87 in
Tread width	1.97 in
Axle hole diameter	0.31 in
Hub length	2.36 in
Hardness of tread (A)	70 Shore A

MAXTECH

PNP200x50-Ø8 HL60 GRIS

EAN 4031582452778



BETTER MOBILITY. BETTER LIFE.

Product Drawings

