PRODUCT INFORMATION

ALPHA

3472PVR200P63

EAN 4031582304923

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●●○
Attrition	●●●○○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Alpha
Type	Swivel castor with total lock, head end of castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	205 kg
Electric Conductive	No
Stainless	No
Load capacity Static	410 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	240 mm
Overall width	96 mm
Overall weight	3.05 kg

HOUSING

Housing Material	Steel sheet, heavy
Fork shape	Broad
Swivel Bearing	Two ball races
Housing Color	Blue passivated
Offset	55 mm
Swivel radius	155 mm
Swivel interference	310 mm
Dome diameter	96 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Solid rubber, black
Bearing	Roller bearing
Axle	Screwed with nut
Wheel Color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	200 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (A)	80 Shore A

FITTING

Fitting type	Medium rectangular plate
Plate length	137 mm
Plate width	105 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

© Copyright 2026 TENTE International GmbH


ALPHA


3472PVR200P63


EAN 4031582304923

Order number 00030718

Product Drawings







© Copyright 2026 TENTE International GmbH