

PRODUCT INFORMATION

NOVATECH

FTP 140x54-Ø20 HL60

EAN 4031582346619



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL


Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	5.51 in
Tread width	2.13 in
Axle hole diameter	0.79 in
Hub length	2.36 in
Body width	2.13 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D
Suitable for	jungheinrich_mic

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	1851.88 lb
Load capacity at 3.7 mph	1543.23 lb
Electric conductive	no
Stainless	no
Load capacity Static	3086.47 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	6.7 lb




PRODUCT INFORMATION

NOVATECH

FTP 140x54-020 H160

EAN 4031582346619

Order number 10833009



BETTER MOBILITY. BETTER LIFE.