PRODUCT INFORMATION

ELASTECH HEAT

IDC 100x35-Ø8,3 HL45 tread-1023 INOX

EAN 4031582348620

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Tread hardness	soft
Body material	Aluminum
Tread material	Damping, heat resistant
Bearing	Precision ball bearing, stainless
Wheel color	Metallic
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.38 in
Axle hole diameter	0.33 in
Hub length	1.77 in
Body width	1.38 in
Hardness of tread (A)	75 Shore A

PERFORMANCE

Roll Performance	●●●●○
Movement noise	●●●●○
Attrition	●●○○○
Corrosion resistance	●●●●●

CORE ATTRIBUTES

Product name	Elastech heat
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	176.37 lb
Electric conductive	no
Stainless	Yes
Load capacity Static	352.74 lb
Temperature range (Minimum)	-22 °F
Temperature range (Maximum)	482 °F
Overall weight	1.25 lb

© Copyright 2026 TENTE International GmbH


ELASTECH HEAT

IDC 100x35-Ø8,3 HL45 tread-1023 INOX

EAN 4031582348620

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH