

# DURATECH

TOP065X32-Ø12 HL32

EAN 4031582453027



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Threadguards	Without threadguard
Diameter	2.56 in
Tread width	1.26 in
Axle hole diameter	0.47 in
Hub length	1.26 in
Hardness of tread (D)	75 Shore D
Bearing type	6201

## PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Duratech
Housing type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	639.34 lb
Load capacity at 3.7 mph	529.11 lb
Load capacity Static	1278.68 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	0.37 lb

## TECHNICAL DRAWINGS

