

PRODUCT INFORMATION

NOVATECH

ETY080x25-Ø25 HL12

EAN 4031582419054



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Steel, iron
Tread Material Mix	Polyurethane, casted
Bearing	Precision ball bearing (RS/2RS)
Diameter	80 mm
Tread width	25 mm
Axle Hole Diameter	25 mm
Hub Length	12 mm
Hardness of tread (A)	92 Shore A

PERFORMANCE

Roll Performance	●●●●○
Movement Noise	●●●○○
Attrition	●●●●○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Load capacity at 3 km/h	160 kg
Electric Conductive	No
Stainless	No
Load capacity Static	320 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.38 kg

NOVATECH

ETY080x25-Ø25 HL12

EAN 4031582419054



BETTER MOBILITY. BETTER LIFE.

Product Drawings

