

# PURETECH AIR

PQR260X85-Ø25 HL74 2PR

EAN 4031582321081  
Order number 00031045



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
Tread hardness	soft
Tread material	Pneumatic tyre, block profile
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	260 mm
Tread width	85 mm
Axle hole diameter	25 mm
Hub length	74 mm
Hardness of tread (A)	55 Shore A

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Puretech air
Type	Wheel
Load capacity at 3 km/h	150 kg
Load capacity Static	150 kg
Overall weight	1.04 kg

# PURETECH AIR

PQR260X85-Ø25 HL74 2PR

EAN 4031582321081  
Order number 00031045



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

