

# NOVATECH

ITP125X50-Ø20 SUPER CONVEX R25

EAN 4031582444858



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Aluminum               |
| Tread material        | Polyurethane, casted   |
| Bearing               | Precision ball bearing |
| Threadguards          | Without threadguard    |
| Diameter              | 4.92 in                |
| Tread width           | 1.97 in                |
| Axle hole diameter    | 0.79 in                |
| Hub length            | 2.36 in                |
| Hardness of tread (A) | 92 Shore A             |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Novatech                      |
| Housing type                | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 1102.31 lb                    |
| Load capacity at 3.7 mph    | 881.85 lb                     |
| Load capacity Static        | 2204.62 lb                    |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 140 °F                        |
| Overall weight              | 0 lb                          |

## TECHNICAL DRAWINGS

