PRODUCT INFORMATION

NOVATECH

RK.ETP078x78-Ø47x16

EAN 4031582330069



Image may differ from the original product

WHEEL

Body material	Undefined
Tread material	Polypropylene, soft
Diameter	3.07 in
Tread width	3.07 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D
Ball bearing diameter	1.85 in
Ball bearing width	0.63 in

PERFORMANCE

Roll Performance	●●●●○
Movement noise	●●●○○
Attrition	●●●●○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1543.23 lb
Load capacity at 3.7 mph	1851.88 lb
Electric conductive	no
Stainless	no
Load capacity Static	3086.47 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	1.49 lb

© Copyright 2026 TENTE International GmbH

NOVATECH

RK.ETP078x78-Ø47x16

EAN 4031582330069

Order number 00832672

Product Drawings





