

PRODUCT INFORMATION

SUPRATECH

PJP100x35-Ø8,3 HL45

EAN 4031582444223



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Supratech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Electric Conductive	No
Stainless	No
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.21 kg

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	100 mm
Tread width	32 mm
Axle Hole Diameter	8 mm
Hub Length	45 mm
Hardness of tread (A)	87 Shore A

SUPRATECH

PJP100x35-Ø8,3 HL45

EAN 4031582444223



BETTER MOBILITY. BETTER LIFE.

Product Drawings

