PRODUCT INFORMATION

LUMINA

6A20POI050B10-11x20

EAN 4031582311310

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●○○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Lumina
Type	Swivel castor
Electric Conductive	No
Stainless	No
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall Height	59 mm
Overall width	55 mm
Overall weight	0.13 kg

HOUSING

Housing Material	Zinc-die-casting / Aluminium
Fork shape	Twin wheel housing, closed
Swivel Bearing	Stem, swiveling
Swivel radius	51 mm
Swivel interference	102 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	50 mm
Tread width	8 mm
Hardness of tread (D)	65 Shore D

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	11 mm

© Copyright 2026 TENTE International GmbH


LUMINA

6A20POI050B10-11x20

EAN 4031582311310

Order number 00073573

Product Drawings



© Copyright 2026 TENTE International GmbH