

NOVATECH

ETX085X85-Ø20 HL95-F

EAN 4031582369649



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing, sealed
Threadguards	With threadguard
Diameter	85 mm
Tread width	85 mm
Axle hole diameter	20 mm
Hub length	95 mm
Hardness of tread (A)	92 Shore A
Sealing type	F
Suitable for	jungheinrich

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Housing type	Wheel
Load capacity at 3 km/h	800 kg
Load capacity Static	1600 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C

NOVATECH

ETX085X85-Ø20 HL95-F

EAN 4031582369649



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

