

MAXTECH

UAC200X40-Ø12,5

EAN 4031582457667



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|-----------------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Precision ball bearing, stainless |
| Threadguards | With threadguard |
| Diameter | 200 mm |
| Tread width | 40 mm |
| Axle hole diameter | 12.5 mm |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 40 Shore D |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Maxtech |
| Type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 350 kg |
| Stainless | ✓ |
| Load capacity Static | 700 kg |
| Temperature range (Minimum) | -40 °C |
| Temperature range (Maximum) | 80 °C |
| Overall weight | 0.83 kg |

MAXTECH

UAC200X40-Ø12,5

EAN 4031582457667



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

