

ELASTECH

XLP125X40-Ø8,3 HL45 ESD



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide, electric conductive
Tread material	Elastic tire, non-marking, antistatic, vulcanized
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	40 mm
Hardness of tread (A)	64 Shore A

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Elastech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	160 kg
Electric conductive	✓
Load capacity Static	320 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	0.649 kg

ELASTECH

XLP125X40-Ø8,3 HL45 ESD



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

XLP125x40-Ø8,3 NL45

