

PURETECH

PVO250X50-Ø20,1 HL58 TRG

EAN 4031582404265



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Solid rubber, black
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	250 mm
Tread width	50 mm
Axle hole diameter	20.1 mm
Hub length	58 mm
Hardness of tread (A)	85 Shore A

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Puretech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	180 kg
Load capacity Static	360 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	2.038 kg

PRODUCT INFORMATION

PURETECH

PVO250X50-Ø20,1 HL58 TRG

EAN 4031582404265

TECHNICAL DRAWINGS

