

PRODUCT INFORMATION

NOVATECH

RK.ETP082x96-Ø52x14

EAN 4031582330656



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Undefined
Tread Material Mix	Polypropylene, soft
Diameter	82 mm
Tread width	96 mm
Hardness of tread (A)	92 Shore A
Ball bearing diameter	52 mm
Ball bearing width	14 mm

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Load capacity at 3 km/h	750 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1500 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C

NOVATECH

RK.ETP082x96-Ø52x14

EAN 4031582330656



BETTER MOBILITY. BETTER LIFE.

Product Drawings

