

PRODUCT INFORMATION

SUPRATECH

PJP200x40-Ø12,5

EAN 4031582457711



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Supratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	160 kg
Electric Conductive	No
Stainless	No
Load capacity Static	320 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.67 kg



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	200 mm
Tread width	40 mm
Axle Hole Diameter	12.5 mm
Hardness of tread (A)	87 Shore A

SUPRATECH

PJP200x40-Ø12,5

EAN 4031582457711



BETTER MOBILITY. BETTER LIFE.

Product Drawings

