

DURATECH

UOP150X44-Ø20 TFR

EAN 4031582390605



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	5.91 in
Tread width	1.73 in
Axle hole diameter	0.79 in
Hub length	2.36 in
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1102.31 lb
Load capacity Static	2204.62 lb
Temperature range (Minimum)	-22 °F
Temperature range (Maximum)	176 °F
Overall weight	1.54 lb

DURATECH

UOP150X44-Ø20 TFR

EAN 4031582390605



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

