

# LINEA CLINIC

5946UAP150R36-34XS S30 D 9002

EAN 4031582348378



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ●   |
| Movement noise       | ● ● ● ● ○   |
| Attrition            | ● ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                                         |
|-----------------------------|-----------------------------------------|
| Product name                | Linea clinic                            |
| Type                        | Swivel caster with central , total lock |
| Standard                    | EN12531 - Hospital Bed Castors          |
| Load capacity at 1.8 mph    | 330.69 lb                               |
| Load capacity at 2.5 mph    | 330.69 lb                               |
| Electric conductive         | no                                      |
| Stainless                   | no                                      |
| Load capacity Static        | 992.08 lb                               |
| Temperature range (Minimum) | 14 °F                                   |
| Temperature range (Maximum) | 104 °F                                  |
| Overall height              | 6.1 in                                  |
| Overall width               | 2.8 in                                  |
| Overall weight              | 2.27 lb                                 |
| Certification               | Tested and monitored by TÜV Süd         |

## HOUSING

|                     |                        |
|---------------------|------------------------|
| Housing Material    | Polyamide              |
| Fork shape          | Twin wheel housing     |
| Swivel bearing      | Precision ball bearing |
| Housing Color       | Gray white (RAL9002)   |
| Offset              | 1.87 in                |
| Swivel radius       | 5 in                   |
| Swivel interference | 10 in                  |
| Dome diameter       | 1.79 in                |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polyamide              |
| Tread material        | Polyurethane, injected |
| Bearing               | Precision ball bearing |
| Wheel color           | Gray white (RAL9002)   |
| Threadguards          | With threadguard       |
| Diameter              | 5.91 in                |
| Tread width           | 0.59 in                |
| Body width            | 0.59 in                |
| Hardness of tread (A) | 92 Shore A             |
| Hardness of tread (D) | 42 Shore D             |

## FITTING

|               |                                                    |
|---------------|----------------------------------------------------|
| Fitting type  | Stem with cam hole for profile bars, short version |
| Bolt diameter | 1.26 in                                            |
| Bolt length   | 1.65 in                                            |

Deutscher  
Designer  
ClubInterzum  
Awardproduct  
design  
awardIF Design  
Award

# LINEA CLINIC

5946UAP150R36-34XS S30 D 9002



EAN 4031582348378

Order number 00034521

Product Drawings



BETTER MOBILITY. BETTER LIFE.



Deutscher  
Designer  
Club



Interzum  
Award



product  
design  
award

IF Design  
Award