PRODUCT INFORMATION

# LINEA CLINIC

## 5946UAP150R36-34XS S30 D 9002

EAN 4031582348378



Image may differ from the original product

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●●● |
| Movement noise | ●●●●○ |
| Attrition | ●●●●○ |
| Corrosion resistance | ●●●○○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product name | Linea clinic |
| Type | Swivel caster with central , total lock |
| Standard | EN12531 - Hospital Bed Castors |
| Load capacity at 1.8 mph | 330.69 lb |
| Load capacity at 2.5 mph | 330.69 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 992.08 lb |
| Temperature range (Minimum) | 14 °F |
| Temperature range (Maximum) | 104 °F |
| Overall height | 6.1 in |
| Overall width | 2.8 in |
| Overall weight | 2.27 lb |
| Certification | Tested and monitored by TÜV Süd |

### HOUSING

| | |
|---|---|
| Housing Material | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel bearing | Precision ball bearing |
| Housing Color | Gray white (RAL9002) |
| Offset | 1.87 in |
| Swivel radius | 5 in |
| Swivel interference | 10 in |
| Dome diameter | 1.79 in |

### WHEEL

| | |
|---|---|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Precision ball bearing |
| Wheel color | Gray white (RAL9002) |
| Threadguards | With threadguard |
| Diameter | 5.91 in |
| Tread width | 0.59 in |
| Body width | 0.59 in |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 42 Shore D |

### FITTING

| | |
|---|---|
| Fitting type | Stem with cam hole for profile bars, short version |
| Bolt diameter | 1.26 in |
| Bolt length | 1.65 in |

Deutscher Designer Club

IF Design Award

Interzum Award

© Copyright 2026 TENTE International GmbH


# LINEA CLINIC


5946UAP150R36-34XS S30 D 9002

EAN 4031582348378

Order number 00034521

**Product Drawings**



Deutscher Designer Club

IF Design Award

Interzum Award