

## NOVATECH


RK.ETP100X40-Ø47X14

EAN 4031582369588

Broj porudžbine 00839713



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

|                            |                     |
|----------------------------|---------------------|
| Materijal za telo          | Nedefinisani        |
| materijal omotaca          | polipropilen, mekan |
| Prečnik                    | 100 mm              |
| Širina omotac              | 40 mm               |
| Teškoća gazećeg omotac (A) | 92 Šor A            |
| Prečnik kuglicni lezaj     | 47 mm               |
| Širina kuglicni lezaj      | 14 mm               |

## PERFORMANSE

|                        |           |
|------------------------|-----------|
| Performanse kotrljanja | ● ● ● ● ○ |
| Buka u pokretu         | ● ● ● ○ ○ |
| Ishrana                | ● ● ● ● ○ |
| otpornost na rdju      | ● ● ● ○ ○ |

## OSNOVNI ATRIBUTI

|                                |          |
|--------------------------------|----------|
| Naziv proizvoda                | Novatech |
| Tip kućišta                    | Tocak    |
| Nosivost na 3 km/h             | 500 kg   |
| Statički Nosivost              | 1000 kg  |
| Temperaturni opseg (Minimalno) | -20 °C   |
| Opseg temperature (maksimalni) | 60 °C    |

## TEHNIČKI CRTEŽI

